



MODEL 3240-Q

KEY FEATURES

- Cost-effective Integrated RF Solution
- Customized RF Isolation Chamber with Integrated Tester Docking
- Up to 120 mm Test Site Pitch
- Up to x8 Parallel Test Site
- 3x3 mm ~ 45x45 mm Package
- Precise Positioning
- Compatible with JEDEC and EIAJ tray

RF SOLUTION INTEGRATED HANDLER

MODEL 3240-Q

The Chroma 3240-Q is a unique and innovative handler with integration of RF/Wireless isolation chamber. The system is configured for up to octal-site with individual isolation for true parallel test. With a streamlined automation sequence, precise Pick & Place system, flexible test site configuration, high throughput and low jam rate, the 3240-Q is ideal for RF/Wireless production test.

The Chroma 3240-Q is also capable of handling various package sizes and types, accurately binning according to customer specified test results. With automatic Input/Output tray stacks, the 3240-Q can accommodate both JEDEC and EIAJ tray standards. Optional temperature control extends the test capability to provide high temperature testing up to 150°C.



Chroma


SPECIFICATIONS

Model	3240-Q
Dimension (WxDxH)	1360 mm x 1390 mm x 1930 mm
Weight	900kg
Facility	Power : AC200V, Single phase 50/60Hz, 10 KVA Max. Compressed Air : 0.5 MPa or higher (dry and clean air) Flow Rate : 150 L/min, constant supply
Applicable Device	Type : CSP, BGA, Gull Wing Package Package Size : 3 mm x 3 mm to 40 mm x 40 mm Package Height : 0.5 mm to 5 mm Lead / Ball pitch : 0.5 mm / 0.4 mm and above
Category	3 categories (1 auto, 2 manual)
Applicable Tray	JEDEC or EIAJ
Index Time	4 sec.
Contact Method	Direct Contact / Drop and Press
Contact Force	Up to 50 ± 1 kgf
Test Site Configuration	4 sites, 2x2, Pitch X = 120 mm, Y = 120mm 8 sites, 4x2, Pitch X = 100 mm, Y = 120mm
PCB Same Site Isolation	-63dB
PCB Different Site Isolation	-91.5dB
Chamber Far Field Isolation	2.4GHz : -80dB @ Distance >250mm (=2*λ2.4GHz)
Jam Rate	1/5,000
Interface	GPIB
Hot Temperature (Option)	Operating Range : Ambient ~ 125°C (Heating Time < within 30 min.) Accuracy : Contact Head ± 3°C, Pre-heater ± 5°C


All specifications are subject to change without notice.

TEST SITE CONFIGURATION

Quad-site



Octal-site



RF CHAMBER ILLUSTRATIONS



Bottom Cover



Top Cover



Loading



Pre-alignment

ORDERING INFORMATION

3240-Q : RF Solution Integrated Handler

HEADQUARTERS
CHROMA ATE INC.
66 Huaya 1st Road, Guishan,
Taoyuan 33383, Taiwan
T +886-3-327-9999
F +886-3-327-8898
www.chromaate.com
info@chromaate.com

HSINCHU BRANCH
6F, No. 5, Technology Rd., Science Park,
Hsinchu City 30078, Taiwan
T +886-3-563-5788
F +886-3-563-5758

U.S.A.
CHROMA ATE INC.(U.S.A.)
7 Chrysler, Irvine,
CA 92618
T +1-949-421-0355
F +1-949-421-0353
www.chromaau.com
info@chromaau.com

SANTA CLARA
3350 Scott Blvd., #601
Santa Clara, CA 95054
T +1-408-969-9998
F +1-408-969-0375

EUROPE
CHROMA ATE EUROPE B.V.
Morsestraat 32,
6716 AH Ede,
The Netherlands
T +31-318-648282
F +31-318-648288
www.chroma.eu.com
sales@chroma.eu.com

JAPAN
CHROMA JAPAN CORP.
472 Nippa-cho, Kouhoku-ku,
Yokohama-shi, Kanagawa,
223-0057 Japan
T +81-45-542-1118
F +81-45-542-1080
www.chroma.co.jp
info@chroma.co.jp

CHINA
CHROMA ATE (SUZHOU) CO., LTD.
Building 7, ShiShan Industrial
Gallery, No. 855, Zhu Jiang Rd.,
Suzhou New District, Jiang Su,
China
T +86-512-6824-5425
F +86-512-6824-0732

CHROMA ELECTRONICS (SHANGHAI) CO., LTD.
3F Building 40, No. 333,
Qin Jiang Rd., Shanghai,
China
T +86-21-6495-9900
F +86-21-6495-3964